

Electroswitch

D4C0606S

Tau Wae:
 Kaihanga / Waitohu:
 Whakaahuatanga hua
 Ngā Rauemi:
 RoHS Tūnga
 Tuhinga mai i
 Te Ara Tuhi

D4C0606S
 Electroswitch
 SWITCH ROTARY 2-6POS 500MA 115V
 D4C0606S.pdf
 Whakahaerehia te kore utu / RoHS
 Hong Kong
 DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o D4C0606S

TAU WAE	D4C0606S
KAIHANGA	Electroswitch
WHAKAAHUATANGA	SWITCH ROTARY 2-6POS 500MA 115V
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
PEPA RARAUNGA	D4C0606S.pdf
WHAKAAETANGA NGAOHIKO - DC	28V
WHAKAAETANGA NGAOHIKO - AC	115V
KĀHUA WHAKAMUTUNGA	Solder Lug
RAUPAPA	D4
PIHANGA WHAKAPAE PAEPAE	Circular - 9.78mm Dia
ĒTAHI INGOA	PA2022
TE KAHA MAHI	-
TAU O NGA TAURANGA	2 ~ 6
TE MAHA O NGA POROWHITA MO TE PORAKA	2
TE MAHA O NGA PEKE	3
MOMO TAE	Panel Mount
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAURUHIA TE INDEX	Adjustable
NGĀ ĀHUATANGA	-
WHAKAAHUATANGA TAIPITOPITO	Rotary Switch 2 ~ 6 Position DP6T 500mA (AC), 1.5A (DC) 115VAC Panel Mount
TE WHAKAARO I MURI I TE PAEPAE	45.24mm
WHAKATAURANGA ONAMATA	500mA (AC), 1.5A (DC)
WHAKAAETANGA WHAKAAETANGA	Shorting (MBB)
WHAKAAETANGA MEA	Brass
WHAKAUTU WHAKAMUTUNGA	Silver
WAEHE MA TE PORAKA	DP6T
TUHINGA O TE MAKA	30°
MOMO KAIHOKO	Round (6.35mm Dia)
TE ROA O TE KAIHOKO	47.63mm

Ngā tūtohu e hāngai ana

Electroswitch D4C0606S	Kaitoha D4C0606S	Kaiwhakarato D4C0606S
Utu D4C0606S	Pikitia D4C0606S	Whakaahua D4C0606S
D4C0606S Pepa Raraunga PDF	D4C0606S Tango Whakahoki	Tapunga D4C0606S
Hokona D4C0606S	Hokona D4C0606S	Hokona Electroswitch D4C0606S
Electroswitch D4C0606S	Kaiwhakarato Electroswitch	Kaitoha Kaatawhai Electroswitch
Electroswitch D4C0606S		

Ngā Hua e hāngai ana

<p>D4C0512N Kaihanga: Electroswitch Whakaahuatanga: SWITCH ROTARY 2-12POS 500MA 115V I roto i te taonga: Out stock</p> <p style="text-align: center; background-color: #d3d3d3; padding: 2px;">RFQ</p>	<p>D4CC-1001 Kaihanga: Omron Automation & Safety Whakaahuatanga: SWITCH SNAP ACTION SPDT 1A 125V I roto i te taonga: 3 pcs</p> <p style="text-align: center; background-color: #d3d3d3; padding: 2px;">RFQ</p>
<p>D4CC-1002 Kaihanga: Omron Automation & Safety Whakaahuatanga: SWITCH SNAP ACTION SPDT 1A 125V I roto i te taonga: 3 pcs</p> <p style="text-align: center; background-color: #d3d3d3; padding: 2px;">RFQ</p>	<p>D4C1202N Kaihanga: Electroswitch Whakaahuatanga: SWITCH ROTARY 2POS 500MA 115V I roto i te taonga: Out stock</p> <p style="text-align: center; background-color: #d3d3d3; padding: 2px;">RFQ</p>
<p>D4C0605S Kaihanga: Electroswitch Whakaahuatanga: SWITCH ROTARY 2-5POS 500MA 115V I roto i te taonga: Out stock</p> <p style="text-align: center; background-color: #d3d3d3; padding: 2px;">RFQ</p>	<p>D4C0612N Kaihanga: Electroswitch Whakaahuatanga: SWITCH ROTARY 2-12POS 500MA 115V I roto i te taonga: Out stock</p> <p style="text-align: center; background-color: #d3d3d3; padding: 2px;">RFQ</p>
<p>D4C1003S Kaihanga: Electroswitch Whakaahuatanga: SWITCH ROTARY 2-3POS 500MA 115V I roto i te taonga: Out stock</p> <p style="text-align: center; background-color: #d3d3d3; padding: 2px;">RFQ</p>	<p>D4C0612S Kaihanga: Electroswitch Whakaahuatanga: SWITCH ROTARY 2-12POS 500MA 115V I roto i te taonga: Out stock</p> <p style="text-align: center; background-color: #d3d3d3; padding: 2px;">RFQ</p>
<p>D4C0503S Kaihanga: Electroswitch Whakaahuatanga: SWITCH ROTARY 2-3POS 500MA 115V I roto i te taonga: Out stock</p> <p style="text-align: center; background-color: #d3d3d3; padding: 2px;">RFQ</p>	<p>D4C0512S Kaihanga: Electroswitch Whakaahuatanga: SWITCH ROTARY 2-12POS 500MA 115V I roto i te taonga: Out stock</p> <p style="text-align: center; background-color: #d3d3d3; padding: 2px;">RFQ</p>
<p>D4C0605N Kaihanga: Electroswitch Whakaahuatanga: SWITCH ROTARY 2-5POS 500MA 115V I roto i te taonga: Out stock</p> <p style="text-align: center; background-color: #d3d3d3; padding: 2px;">RFQ</p>	<p>D4C0606N Kaihanga: Electroswitch Whakaahuatanga: SWITCH ROTARY 2-6POS 500MA 115V I roto i te taonga: Out stock</p> <p style="text-align: center; background-color: #d3d3d3; padding: 2px;">RFQ</p>