



Optek Technology / TT Electronics

## OP643SL

Tau Wae:

Kaihanga / Waitohu:

Whakaahuatanga hua

Ngā Rauemi:

RoHs Tūnga

Tuhinga mai i


Te Ara Tuhi

OP643SL

Optek Technology / TT Electronics

PHOTOTRNS SILCN NPN HERMETC PILL

 OP643SL.pdf

 Whakahaerehia te kore utu / RoHS


Hong Kong

DHL/Fedex/TNT/UPS/EMS

### TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.













### Ngā whakaaturanga o OP643SL

TAU WAE	OP643SL
KAIHANGA	Optek Technology / TT Electronics
WHAKAAHUATANGA	PHOTOTRNS SILCN NPN HERMETC PILL
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Whakahaerehia te kore utu / RoHS
PEPA RARAUNGA	 OP643SL.pdf
WAIMOTU	890nm
NGAOHIHI - TE WHAKATERE EMITTER BREAK (MAX)	25V
TIROHIA TE ANGLE	-
RAUPAPA	*
MANA - MAX	50mW
PACKAGING	Bulk
PAA / CASE	Pill
ĒTAHI INGOA	365-2014 OP643SL-ND
WHAKATAKOTORANGA	Top View
TAE MAHI	-65°C ~ 125°C (TA)
MOMO TAE	Surface Mount
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
TE TAE KAITUKU TAEKE	10 Weeks
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free / RoHS Compliant
WHAKAAHUATANGA TAIPITOPITO	Phototransistor 890nm Top View Pill
I TEIE NEI - DARK (ID) (MAX)	100nA
I TEIE NEI - KOHIKOHI (IC) (MAX)	50mA

### Ngā tūtohu e hāngai ana

Optek Technology / TT Electronics OP643SL	Kaitoha OP643SL	Kaiwhakarato OP643SL
Utu OP643SL	Pikitia OP643SL	Whakaahua OP643SL
OP643SL Pepa Raraunga PDF	OP643SL Tango Whakahoki	Tapunga OP643SL
Hokona OP643SL	Hokona OP643SL	Hokona Optek Technology / TT Electronics OP643SL
Optek Technology / TT Electronics OP643SL	Kaiwhakarato Optek Technology / TT Electronics	Kaitoha Kaatawhai Optek Technology / TT Electronics
Optek Technology / TT Electronics OP643SL	OPTEK Technologies OP643SL	Optek Technology OP643SL
TT Electronics/Optek Technology OP643SL		

### Ngā Hua e hāngai ana

 <p><b>OP641SL</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: Out stock</p> <p><b>RFQ</b></p>	 <p><b>OP600B</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: 16 pcs</p> <p><b>RFQ</b></p>
 <p><b>OP602TX</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: Out stock</p> <p><b>RFQ</b></p>	 <p><b>OP604TXV</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: Out stock</p> <p><b>RFQ</b></p>
 <p><b>OP642SL</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: Out stock</p> <p><b>RFQ</b></p>	 <p><b>OP602TXV</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: Out stock</p> <p><b>RFQ</b></p>
 <p><b>OP644SL</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL PAK I roto i te taonga: 879 pcs</p> <p><b>RFQ</b></p>	 <p><b>OP603TX</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: Out stock</p> <p><b>RFQ</b></p>
 <p><b>OP600C</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: Out stock</p> <p><b>RFQ</b></p>	 <p><b>OP603TXV</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: Out stock</p> <p><b>RFQ</b></p>
 <p><b>OP604S</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: Out stock</p> <p><b>RFQ</b></p>	 <p><b>OP604TX</b> Kaihanga: Optek Technology / TT Electronics Whakaahuatanga: PHOTOTRNS SILCN NPN HERMETC PILL I roto i te taonga: Out stock</p> <p><b>RFQ</b></p>

