

E-Switch

TL6700NF260QJ

Tau Wae:
 Kaihanga / Waitohu:
 Whakaahuatanga hua
 Ngā Rauemi:
 RoHs Tūnga
 Tuhinga mai i
 Te Ara Tuhi

TL6700NF260QJ
 E-Switch
 SWITCH TACTILE SPST-NO 0.05A 12V
[PDF](#) 1.TL6700NF260QJ.pdf
[PDF](#) 2.TL6700NF260QJ.pdf
 Whakahaerehia te kore utu / RoHS
 Hong Kong
 DHL/Fedex/TNT/UPS/EMS

TONO MO TE WHAKAHUA

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

Ngā whakaaturanga o TL6700NF260QJ

| | |
|--|--|
| TAU WAE | TL6700NF260QJ |
| KAIHANGA | E-Switch |
| WHAKAAHUATANGA | SWITCH TACTILE SPST-NO 0.05A 12V |
| WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA | Whakahaerehia te kore utu / RoHS |
| PEPA RARAUNGA | PDF 1.TL6700NF260QJ.pdf PDF 2.TL6700NF260QJ.pdf |
| KĀHUA WHAKAMUTUNGA | J Lead |
| WHAKAWHITI MAHERE | 0.35mm |
| WHAKAWHITI MAHINGA | Off-Mom |
| RAUPAPA | TL6700 |
| PACKAGING | Tape & Reel (TR) |
| WHAKAAHUATANGA | 6.90mm x 6.20mm |
| ĒTAHI INGOA | EG4382TR |
| TAE MAHI | -20°C ~ 70°C |
| TE KAHA MAHI | 260gf |
| MOMO TAE | Surface Mount |
| TAUMATA WHAKAARO MOE (MSL) | 1 (Unlimited) |
| TE MAHI MOMO | 100,000 Cycles |
| TE TAE KAITUKU TAEKE | 11 Weeks |
| WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA | Lead free / RoHS Compliant |
| TIAKI INGOA | - |
| WHAKAKAMAHI WHAKAKUKU (NOMINAL) | - |
| MOMO WHAKAMARAMA, TAE | - |
| WHAKAAHUATANGA | Non-Illuminated |
| NGĀ ĀHUATANGA | Process Sealed |
| WHAKAAHUATANGA TAIPITOPITO | Tactile Switch SPST-NO Top Actuated Surface Mount |
| WHAKAPĀ ATU @ WHAKAOHO | 0.05A @ 12VDC |
| TAKAHANGA | SPST-NO |
| MOMO KAIHOKO | Flush |
| TE WHAKATAIRANGA MAHI | Top Actuated |
| TUHINGA KAIRANGI | Silicon Rubber |
| TE RAITA MAHI, TE MATAU MATAU | - |
| TEITEI O TE KAIHOKOHOKO MAI I PCB, POUTURU | 2.60mm |

Ngā tūtohu e hāngai ana

| | | |
|---------------------------------|-------------------------------|-------------------------------|
| E-Switch TL6700NF260QJ | Kaitoha TL6700NF260QJ | Kaiwhakarato TL6700NF260QJ |
| Utu TL6700NF260QJ | Pikitia TL6700NF260QJ | Whakaahua TL6700NF260QJ |
| TL6700NF260QJ Pepa Raraunga PDF | TL6700NF260QJ Tango Whakahoki | Tapunga TL6700NF260QJ |
| Hokona TL6700NF260QJ | Hokona TL6700NF260QJ | Hokona E-Switch TL6700NF260QJ |
| E-Switch TL6700NF260QJ | Kaiwhakarato E-Switch | Kaitoha Kaatawhai E-Switch |
| E-Switch TL6700NF260QJ | | |

Ngā Hua e hāngai ana

| | |
|---|---|
| <p>TL6700NF260QG Kaihanga: E-Switch Whakaahuatanga: SWITCH TACTILE SPST-NO 0.05A 12V I roto i te taonga: Out stock RFQ</p> | <p>TL6700AF160QG Kaihanga: E-Switch Whakaahuatanga: SWITCH TACTILE SPST-NO 0.05A 12V I roto i te taonga: Out stock RFQ</p> |
| <p>TL6330AF200Q Kaihanga: E-Switch Whakaahuatanga: SMT MINIATURE IP67 2.80MM X 4.60 I roto i te taonga: Out stock RFQ</p> | <p>TL6700NF160QG Kaihanga: E-Switch Whakaahuatanga: SWITCH TACTILE SPST-NO 0.05A 12V I roto i te taonga: Out stock RFQ</p> |
| <p>TL6700AF260QG Kaihanga: E-Switch Whakaahuatanga: SWITCH TACTILE SPST-NO 0.05A 12V I roto i te taonga: Out stock RFQ</p> | <p>TL6304CF300QG Kaihanga: E-Switch Whakaahuatanga: SWITCH TACTILE SPST-NO 0.05A 12V I roto i te taonga: Out stock RFQ</p> |
| <p>TL6700AF260QJ Kaihanga: E-Switch Whakaahuatanga: SWITCH TACTILE SPST-NO 0.05A 12V I roto i te taonga: Out stock RFQ</p> | <p>TL6700AF160QJ Kaihanga: E-Switch Whakaahuatanga: SWITCH TACTILE SPST-NO 0.05A 12V I roto i te taonga: Out stock RFQ</p> |
| <p>TL6304BF200QJ Kaihanga: E-Switch Whakaahuatanga: SWITCH TACTILE SPST-NO 0.05A 12V I roto i te taonga: Out stock RFQ</p> | <p>TL6700NF160QJ Kaihanga: E-Switch Whakaahuatanga: SWITCH TACTILE SPST-NO 0.05A 12V I roto i te taonga: Out stock RFQ</p> |
| <p>TL6304BF300QG Kaihanga: E-Switch Whakaahuatanga: SWITCH TACTILE SPST-NO 0.05A 12V I roto i te taonga: Out stock RFQ</p> | <p>TL6304NF300QJ Kaihanga: E-Switch Whakaahuatanga: SWITCH TACTILE SPST-NO 0.05A 12V I roto i te taonga: Out stock RFQ</p> |